

Piccolo metal tubes





Assembling instructions

- The Piccolo swivel is to be pressed into the tube
- 1. To be welded to metal legs (la) / base (lb)
- 2. To be assembled to a center hole of base Ø50mm Conicity 1°26′16″
- 3. To be fastened to a base by an M12 screw
- Ask for our assembly instructions

Product information

Tapered metal tube models for Piccolo swivels, made from $50.8 \times 2,00$ or $50.0 \times 2,00$ mm pipes.

Form Product code

1 * cone 510 065 (minimum length 70mm)

 1 * cone
 510 165

 2 * cone
 510 165-C

 1 * cone M12
 510 165-M12

Cylindric Ø44,5mm 510 445 (length on request)

If welded, tube can deform and needs to be reshaped.

Specifications

- MK6 = 1°29′36″
- Standard made from metal pipe Ø50,8mm
- Wall thickness of standard pipe 2mm
- Raw metal surface, II -class for painting

Options

- Surface: painted or chrome (matt/shiny). Other surfaces on request
- Length
- Upper conicity of tube could be made deeper to assemble the swivel at a lower level
- Also available in Aluminium or stainless steel K320

Mekrapid Products

www.mekrapid.fi

info@mekrapid.fi

Depågatan 10 FI-68600 Jakobstad Finland